



## ANSMANN Future T400FR

- High-quality, rechargeable aluminium torch for professional use
- Latest high-performance LEDs
- Seamless focussing by turning the lamp head, from a precise point of light to homogeneous floodlighting
- Large on/off switch and non-slip exterior for maximum user comfort even when wearing gloves, ideal for single-handed use
- Four lighting functions: 100% / 30% lighting power, strobe and SOS functions
- Brightness: 400 Lumens (100%), 130 Lumens (30%)
- Battery life ca. 3 h (100%), ca. 9 h (30%)
- Lighting range: up to 175 m
- Protection rating: IPX4 / impact-resistant up to 1m drop height
- Including replaceable 18650 Li-Ion rechargeable battery pack, micro-USB cable and wrist strap
- Packaged in an attractive, hanging folded box with viewing window
- 3 year ANSMANN-Germany manufacturer's guarantee

### INFORMATION

Product name:	Future T400FR	Product:	32 × 32 × 168.4 mm / 226g
Part No.:	1600-0150	Packing + Product:	125 × 38 × 272 mm / 312g
EAN-Code:	4013674105977	Packing Unit:	30 (410 × 392 × 300 mm)
Customs tariff number:	85131000		
Material Group:	88		
Package contents:	Torch, Micro-USB cable, ANSMANN 18650 3.6V Li-Ion rechargeable battery pack & wrist strap.		