

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-423

Designed to make the selection of hand protection easy

Previously known as: Puretough™P3000



Cut



Medium Duty

Whatever industry, the HyFlex indicator system helps the wearer to select the right protection for the job.

- The smart combination of abrasion and cut resistance. Provides not only the protection needed in dry and slightly oily environments, but also educates workers to understand risk levels
- Designed to make the selection of hand protection easy. The indicator system on these Hyflex gloves simplifies the selection of the right glove for the job for increased worker safety
- The color indicator system on the glove ensures the wearer of always having the appropriate cut level performance



Industries

- Automotive
- Machinery and Equipment
- Metal fabrication

Applications

- Handling parts with sharp, rough edges
- Metalworking & assembly operations
- Adjusting parts, systems
- Adjusting systems and screwing
- Applying finish to materials, products

HyFlex®

ADVANCED MECHANICAL PROTECTION

11-423

Designed to make the selection of hand protection easy

Previously known as: Puretough™P3000

Key Features

- Water-based process is environmentally friendly, and has an innovative coating.
- Silicone-free and DMF-free.
- Excellent abrasion resistance.
- 11-423 is made from high performance and highly visible fibres resisting to the heat up to 100°C (212°F).
- Also available in vend pack

Vulcanization Chemical Accelerators

- Natural rubber proteins (in knitwrist elastic)
- Zinc Diethyldithiocarbamate

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

Performance Standards & Regulatory Compliance

REACH Compliant



Specifications

BRAND STYLE	DESCRIPTION	Gauge	SIZE	LENGTH	COLOR	PACKAGE
HyFlex® 11-423	Finishing: Palm Coated Coating Material: Water-Based polyurethane and nitrile Liner Material: Polyamide, Fiber glass Cuff Style: Knitwrist	13	6, 7, 8, 9, 10, 11	225-265 mm; 9.25-10.43 inches	Grey	• 12 pairs in a bag; 12 bags in a carton

For additional information visit us at www.ansell.com, or call us at

Europe, Middle East & Africa Region

Ansell Healthcare Europe NV
Riverside Business Park
Blvd International, 55
1070 Brussels, Belgium
T: +32 (0) 2 528 74 00
F: +32 (0) 2 528 74 01

North America Region

Ansell Healthcare Products LLC
111 Wood Avenue South,
Suite 210
Iselin, NJ 08830, USA
T: +1 800 800 0444
F: +1 800 800 0445

Australia

Ansell Limited
Level 3,678 Victoria Street,
Richmond, Vic, 3121
Australia
T: +61 1800 337 041
F: +61 1800 803 578

Asia Pacific Region

Ansell Global Trading Center
(Malaysia) Sdn Bhd
Prima 6, Prima Avenue
Block 3512, Jaijan Teknokrat 6
T: +603 8310 6688
F: +603 8310 6699

Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.
Blvd. Bernardo Quintana No. 7001-C,
Q7001 Torre II,
Suites 1304, 1305 y 1306,
Col. Centro Sur, c.p. 76079
Queretaro, Qro. Mexico
T: +52 442 248 1544 / 248 3133

Canada

Ansell Canada
105 Lauder
Cowansville, QC J2K 2K8
Canada
T: +1 800 363 8340
F: +1 800 267 3551

Ansell, ® and ™ are trademarks owned by Ansell Limited or one of its affiliates. US Patented and US and non-US Patents Pending: www.ansell.com/patentmarking © 2021 Ansell Limited. All Rights Reserved.

Neither this document nor any other statement made herein by or on behalf of Ansell should be construed as a warranty of merchantability or that any Ansell product is fit for a particular purpose. Ansell assumes no responsibility for the suitability or adequacy of an end user's selection of gloves for a specific application.

Technologies

