



HP LaserJet 1160 Printer (Q5933A) - Specifications



- The HP LaserJet 1160 Printer provides the dependable, high-quality output you are used to expecting from HP, along with the performance you need, all at an affordable price.
- Get professional-looking documents with the HP LaserJet 1160 Printer, featuring 1200 dpi effective output quality*. With Instant-on technology and up to 19 ppm A4, your print job is finished before many printers have even started printing.
- The highly-reliable HP LaserJet 1160 Printer easily fits into your office environment, supporting a wide range of operating systems and offering simple connectivity via USB and parallel ports - all at a great price.

Specifications & Warranty

Printing System

Print technology	Monochrome Laser
Print Speed (Black, Normal Quality, A4)	Up to 19 ppm
First page out, A4 size	8.5 sec
processor speed	133 MHz
Processor	Motorola V4 Coldfire
Print Quality (Black, Best Quality)	.
pages per month	10000

Paper handling / media

Media Types supported	Plain paper, envelopes, transparencies, cardstock, postcards, labels
Media size, tray 1	A4, A5, A6, B5, B6 envelopes (C5, DL), 76 x 127 to 216 x 356 mm

Media size, tray 2	A4, A5, B5, 147 x 211 to 216 x 356 mm
--------------------	---------------------------------------

Standard Input Capacity	Up to 250
-------------------------	-----------

Maximum Input Capacity	Up to 250
------------------------	-----------

Standard Output Capacity	Up to 125
--------------------------	-----------

Duplex Print Options	Manual (driver support provided)
----------------------	----------------------------------

Memory / print languages / typefaces

Standard Memory	16 MB
-----------------	-------

Maximum Memory	16 MB
----------------	-------

Standard Printer Languages	HP PCL 5e
----------------------------	-----------

Typefaces	26 scalable fonts built in
-----------	----------------------------

Connectivity

Standard Connectivity	Full-speed USB port (compatible with USB 2.0 specifications), IEEE 1284-B compliant parallel port
-----------------------	---

Optional Connectivity	HP Jetdirect external print servers; HP wireless print servers; Bluetooth wireless printer adapter.
-----------------------	---

Compatible Network Operating Systems	Via HP Jetdirect print server: Microsoft Windows 98, Me, 2000, XP, NT 4.0 (print driver only), Microsoft Windows XP 32-Bit, XP 64-Bit (print driver only), Server 2003, Mac OS 9, OS X v 10.1, 10.2, 10.3; optional: Novell® NetWare 3.2, 4.2, 5.x, 6; Red Hat Linux 6.x and later; SuSE Linux 6.x and later; HP-UX 10.20, 11.x; Solaris™ 2.5x, 2.6, 7, 8; IBM® AIX 3.2.5 and later; MPE-iX
--------------------------------------	---

Network interface	Optional HP Jetdirect external print server
-------------------	---

Minimum System Requirements	Microsoft Windows 98, Pentium, 166 MHz, 64 MB RAM; Mac OS 9.1 and later, 96 MB RAM; Mac OS X v 10.1 and later: 128 MB RAM, CD-ROM drive
-----------------------------	---

Other technical information

Control Panel	Comprised of 3 lights and 2 buttons (Go and Cancel); these lights produce patterns that identify the printer's status (Toner, Attention, Ready)
---------------	---

Power consumption	0 watts (off), 6 watts maximum (powersave/standby), 345 watts maximum (printing)
-------------------	--

Power Requirements	Input voltage 110 to 127 VAC (+/- 10%), 50/60 Hz (+/- 2 Hz); 220 to 240 VAC (+/- 10%), 50/60 Hz (+/- 2 Hz)
--------------------	--

Dimensions (w x d x h)	350 x 355 x 256 mm
------------------------	--------------------

Weight	10.5 kg
--------	---------

Operating Temperature	10 to 32.5° C
-----------------------	---------------

Range

Recommended
Operating Temperature
Range 10 to 32.5° C

Storage Temperature
Range 0 to 40° C

Energy Star Certified Yes

Software Included HP printer software on CD-ROM includes HP installer/uninstaller, drivers, HP Toolbox for diagnostic status and configuration, control panel simulator, help, documentation

Box Content HP LaserJet 1160 Printer, power cord, HP LaserJet Print Cartridge, user's guide, printer documentation and software on CD-ROM, 250-sheet input tray, single-sheet priority input tray

Warranty One-year standard bench repair and return to HP authorised service centre warranty.

At a glance

Model	Model differences
<u>HP LaserJet 1160 Printer (Q5933A)</u>	Full-speed USB port (compatible with USB 2.0 specifications), IEEE 1284-B compliant parallel port Manual (driver support provided)

[Privacy statement](#)

[Using this site means you accept its terms](#)

[Feedback to webmaster](#)

© 2005 Hewlett-Packard Development Company, L.P.