

M18 STSO-OB

M18™ FORCE LOGIC™ STRUT SHEAR

- Cleanest and safest way to cut strut profiles
- Compatible with 41x41 mm, 41x21 mm, 41x22 mm strut
- Compatible with commonly available strut manufacturers in the specified dimensions
- Shears pre- and hot dipped galvanised strut until 3.0 mm wall thickness
- All day run time of over 200 cuts on a single M18™ 5.0 Ah battery
- Cuts 41x41 mm strut in under 5 seconds
- Tool design allows it to be used on ground or as a benchtop solution
- Perfect weight distribution allows comfortable transport of the tool
- Integrated fixpoint to clamp tool on pipe stand to shear in convenient height
- ONE-KEY™ tool tracking & security offers a free of charge cloud-based tracking network and inventory management platform for your tools. ONE-KEY™ also features a remote locking functionality
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™



Cuts per battery	200
Cutting capacity (mm)	41x41; 41x22, 41x21
Cutting time (s)	<5
Standard equipment	41x41 mm cutting die set
Weight with battery pack (EPTA) (kg)	11.6 (M18 B5)
Kit included	No batteries supplied, No charger supplied, Tool bag
Article Number	4933492097

