

FEATURES

- Steel clevis fasteners
- Spring clip
- M5 x 0.8 rod connection thread
- Ball diameter of 5mm
- Overall length of 26mm
- Overall width of 10mm
- Zinc finish for corrosion-resistant finish

RS PRO Steel M5 x 0.8 Clevis, 26mm x 10mm

RS Stock No.: 312-0258



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The high quality of these clevis fasteners from the RS PRO series makes them ideal for applications that demand compact yet robust components. They're U-shaped in design and have two holes for a pin to be inserted. This allows a flexible connection to be created when materials are joined together, as the parts rotate about the axis of the pin.

General Specifications

Accessory Type	Clevis
Rod Connection Thread	M5 x 0.8
Material	Steel
Finish	Zinc
Applications	Food, medical, petrochemical aviation and agriculture industries

Mechanical Specifications

Overall Length	26mm
Overall Width	10mm
Ball Diameter	5mm

Approvals

Compliance/Certifications	BS970 PE 1 1983 220 MO7, BS970 PE 5 1972 270 A72, DIN 71752
----------------------------------	---



Dimensions (mm)											
Thread A	B	C	D	E	Ø F	G	H	J	K	L	Ø M
M5x0.8	26	10	10	5.14/5.26	5	7.5	9	20	19	12	5

