

Pin Headers

3.5/3.81mm pitch



SPECIFICATION:

Material

Housing	PA66, UL94V-0
Pin Header	Brass, Tin Plated

Electrical

Standard	IEC	
Rated Voltage	300V	250V
Rated Current	8A	10A
Withstand Voltage	AC2000V/1Min	
Contact Resistance	20mΩ	
Insulation Resistance	500MΩ/DC500V	

Mechanical

Temperature Range	-40°C~+105°C
Max Soldering Temperature	+250°C for 5sec

Size

Pitch	3.5mm(.138"), 3.81mm(.150")
Poles	2P-12P

