


## 9780 Max. 18 VA

### AC/AC ADAPTER

- 230 VAC input voltage
- Available with EU and UK terminals
- Compliance with relevant worldwide safety standards
- Exchangeable output plugs, providing:
  - reduced stocking requirements
  - short delivery lead times
  - snap-locks for added safety



<b>Technical specifications</b>	<b>12 V</b>	<b>12 V</b>
Input voltage:	230 VAC, 50 Hz	
Output voltage:	12VAC	12VAC
Max.output power:	12VA	18VA
Load current:	1A	1,5A
Temperature range:	-10°C to +40°C	
Protection:	Protected against internal short circuit by thermal fuse in primary	
Insulation class	II	
Electrical safety	EN 60950	
EMC, Emission	EN50081-1	
EMC, Immunity	EN50082-1	
Mains connections:	EU and UK	
Output terminals:	Secondary cable w/snap-on plugs	
Dimensions (EU mod):	63x51x42mm	74x58x47mm
Weight:	320g	460g