Features

- Heavy-duty lockout hasp constructed from 316 stainless steel.
- Designed for use in highly corrosive and extreme environments.
- Supports up to 7 padlocks (maximum 7 mm shackle diameter).
- Compatible with switchgear and lockout gadgets with ≥ 5.25 mm hole size
- Tamperproof configuration ensures complete group lockout security.
- Suitable for offshore platforms, marine industries, mining sites, and chemical plants.
- Provides long-term reliability in harsh industrial settings.

RS PRO Heavy-Duty Stainless-Steel Lockout Hasp - 7 Hole

RS Stock No.: 0802198



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- ***Marine-Grade 316 Stainless Steel Construction*** *- Manufactured from* ***marine-grade AISI 316 stainless steel****, delivering exceptional corrosion resistance and durability in aggressive environments.*
- ***Engineered for Harsh & Corrosive Conditions*** *- Ideal for* ***offshore installations, mining operations, marine facilities, and chemical plants*** *where exposure to moisture, salt, and corrosive agents is common.*
- ***7-Hole Group Lockout Capability*** *- Designed to accommodate* ***up to 7 individual padlocks*** *simultaneously, enabling safe and effective multi-person lockout procedures.*
- ***Wide Compatibility with Isolation Points*** *- Fits most* ***switchgear and lockout devices*** *with a minimum hole size of* ***5.25 mm****, ensuring versatile application.*
- ***Tamper-Resistant Design*** *- Secure construction ensures the hasp remains locked in place* ***until all applied padlocks are removed****, maintaining strict group lockout integrity.*
- ***Heavy-Duty Industrial Design*** *- Robust stainless-steel build ensures long service life and reliable mechanical performance under demanding conditions.*

General Specifications


Type	Lockout Hasp
Material	Stainless Steel
Colour	Red
Padlock holes	7
Package	Individual Box

Mechanical Specifications

Dia (Jaw Size)	31 / 38 mm
Width	57mm
Height	110mm
Shackle Dia	5mm
Accepts Shackle Dia	7mm
Weight	114 Grams

Operation Environment Specifications

Withstand temperature	-40°C to 120°C


ON
OFF
DANGER
LOCKED OUT
DO NOT REMOVE