

## Datasheet

### **RS Pro Straight 50 $\Omega$ Panel Mount Bulkhead Fitting BNC Connector, jack, Clamp Termination RG58A**

RS Stock No: **546-3945**



## Product Details

RS Pro panel mount bulkhead fitting BNC connector has a nickel plated body, gold plated centre contact and is suitable for RG58A cables. This 50  $\Omega$  straight BNC connector comes with cable jack, clamp termination.

## Features and Benefits

- Nickel plated body
- Gold plated centre contact
- Jack, clamp termination

## Specifications:

Body Orientation	Straight
Body Plating	Nickel
Bulkhead	Yes
Cable Type	RG58A
Contact Material	Brass
Contact Plating	Gold
Gender	Female
Impedance	50 $\Omega$
Mounting Type	Panel Mount
Operating Frequency	4 GHz
Polarity	Normal
Termination Method	Clamp
Contact Resistance	1.5 m $\Omega$ (Maximum Central), 0.5 m $\Omega$ (Maximum Outer)
Insulation Material	PTFE (Internal)
Insulation Resistance	5000 M $\Omega$
Number of Functions	500
Operating Temperature Range	-65 to +85°C
Standards Met	RoHS Compliant
Voltage Rating	750 V (Insulation), 335 V (Working)