



## 8mm (1/4") Fixed Base Router

D26200-QS

Aluminium motor housing can be transitioned into a plunge router attachment for increased versatility ( available separately )

Multiple spindle lock detents enables quick and simple router bit changes  
Variable speed control 16,000 to 27,000 enables router bit to be Optimized for application

Dual LED lights increase visibility around the router bit during operation for increased accuracy

Large 100mm D-Base design to allow the user maximum router support on the work piece



Sound Pressure Uncertainty	3 dB(A)
----------------------------	---------

Sound Pressure	77 dB(A)
----------------	----------

Uncertainty K 1 (Vibration)	2.7 m/s <sup>2</sup>
-----------------------------	----------------------

Power Input	900W
-------------	------

Power Source	Corded
--------------	--------

No Load Speed	16000-27000 Rpm
---------------	-----------------