




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	13JAN2016	NK	RH



- 1
- WORKING TEMPERATURE: 105° C
- 2
- VOLTAGE: 600V MAX.
- 3
- COLOR: RED
- 4
- WIRE RANGE: #22-#6AWG MAX.1#8
W/3#12 STR MIN.3#20
- 5
- SPRING INSERT: STEEL

2299512-1 AS SHOWN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 13JAN2016	 TE Connectivity			
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK HILL RYAN 13JAN2016	NAME			
		APVD HILL RYAN 13JAN2016				
	0 PLC ± - 1 PLC ± 0.2[.007] 2 PLC ± 0.4[.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC —	CPGI—WC—CG—RD—BULK			
		APPLICATION SPEC —				
MATERIAL UL 94V-2 FLAME-RETARDANT THERMOPLASTIC SHELL	FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-2299512	RESTRICTED TO —
		CUSTOMER DRAWING				
			SCALE 2:1	SHEET 1 OF 1	REV A	