

894 36

Single open ended spanner

metric

Code
6576700

ETIM
EC002130

EAN
4010886657676

UNSPSC
27-11-17-06

Country of origin
Germany

eCl@ss
21-04-01-01

Customs tariff number
82041100



Article description

- Acc. to DIN 894, ISO 3318
- Manganese phosphate finish up to 38 mm, steel-grey up from 41 mm
- Size 10 - 135 mm with angling hole
- Carefully forged and professionally machined:
- Jaw: ground precisely to exact nominal size for optimum contact areas
- Jaw set at 15°
- Secure grip thanks to profile shaft - very ergonomic and handy
- Overloading indicated by deformation
- * not standardised

Article information

Contents (Qty of pieces)	1	Standard	DIN 894 ISO 3318
Net weight [kg]	0,392 kg	Width across flats 1 [mm]	36
Total length [mm]	301 mm	Head height 1 [mm]	12,8 mm
Total width [mm]	70 mm	Width of head 1 [mm]	74,0 mm
Total height [mm]	14 mm	Jaw set	15 °
Surface	manganese phosphated	Ratchet function	no
Material	Vanadium steel 31CrV3		