



## CRI-H200R - HIGH CRI SENSOR HEADTORCH



**200**  
LUMEN



**3H**  
RUNTIME



**27M**  
RANGE



**IP65/IPK07**  
IP RATING

- 200 Lumen white COB LED
- High CRI 96+ 3 coloured COB LED
- CCT range: 2500K / 4500K / 6500K
- Sensor mode for hands-free operation
- 60° Rotational head
- Fully adjustable non-slip silicone headband included
- IP65 dust & water resistant
- IK07 Shock resistant

- Red-to-Green charging indicator light
- Quick 1A micro-USB rechargeable - 3 hours charge time
- 1m micro-USB cable included

**BATTERY** 3.7v 1500mAh Li-Polymer Rechargeable Battery

**WEIGHT** 110g

**DIMENSION** Headtorch: 48 x 79 x 46mm



RUBBERISED HEAD BRACKET