

# Suction cup with connector OGVM-50-A-N-G38F

Part number: 8211027

**FESTO**



## Data sheet

 [General operating condition](#)

| Feature                                     | Value                                            |
|---------------------------------------------|--------------------------------------------------|
| Height compensator for suction cup          | 11.5 mm                                          |
| Min. workpiece radius                       | 35 mm                                            |
| Nominal size                                | 7 mm                                             |
| Suction cup diameter                        | 50 mm                                            |
| Suction cup volume                          | 15 cm <sup>3</sup>                               |
| Position of connection                      | On top                                           |
| Mounting position                           | Any                                              |
| Symbol                                      | 00991485                                         |
| Suction cup shape                           | Round protective bellows 1.5-fold                |
| Operating pressure                          | -0.095 MPa ... 0 MPa                             |
| Operating pressure                          | -0.95 bar ... 0 bar                              |
| Operating pressure                          | -13.775 psi ... 0 psi                            |
| Nominal operating pressure                  | -0.06 MPa                                        |
| Nominal operating pressure                  | -0.6 bar                                         |
| Nominal operating pressure                  | -8.7 psi                                         |
| Operating medium                            | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Corrosion resistance class CRC              | 2 - Moderate corrosion stress                    |
| LABS (PWIS) conformity                      | VDMA24364-A1/A2-L                                |
| Ambient temperature                         | -20 °C ... 80 °C                                 |
| Holding force at nominal operating pressure | 90 N                                             |
| Lateral force at nominal operating pressure | 72 N                                             |
| Product weight                              | 36 g                                             |
| Type of mounting                            | Via vacuum port                                  |
| Vacuum connection                           | Female thread G3/8                               |
| Colour                                      | Black                                            |
| Shore hardness                              | 60 +/-5                                          |
| Material screwed plug                       | Wrought aluminium alloy                          |
| Note on materials                           | RoHS compliant                                   |
| Material suction cup                        | NBR                                              |