

## SEK CAB FLAT COLOR TW AWG28/7 64P 30,48m



Image is for illustration purposes only. Please refer to product description.

|                    |   |
|--------------------|---|
| Part number        | 09 18 064 7006  |
| Specification      | SEK CAB FLAT COLOR TW AWG28/7<br>64P 30,48m                                   |
| HARTING eCatalogue | <a href="https://harting.com/09180647006">https://harting.com/09180647006</a> |

### Identification

|                          |                     |
|--------------------------|---------------------|
| Category                 | System cabling      |
| Element                  | Bulk cables         |
| Specification            | Not assembled       |
| Type of cable            | Copper cable (flat) |
| Description of the cable | Twisted pair        |

### Version

|                 |          |
|-----------------|----------|
| Cable length    | 30.48 m  |
| Number of cores | 64       |
| Core structure  | AWG 28/7 |

### Technical characteristics

|                         |                  |
|-------------------------|------------------|
| Impedance               | 122 $\Omega$     |
| Limiting temperature    | -20 ... +105 °C  |
| Signal run time @ 20 °C | $\leq 5.35$ ns/m |

### Material properties

|   |              |
|---|--------------|
| Material (cable)                          | PVC          |
| Colour (cable)                            | Colour coded |
| Material flammability class acc. to UL 94 | VW-1         |
| RoHS                                      | compliant    |
| ELV status                                | compliant    |
| China RoHS                                | e            |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |               |
|--------------------------------------|---------------|
| REACH Annex XVII substances          | Not contained |
| REACH ANNEX XIV substances           | Not contained |
| REACH SVHC substances                | Not contained |
| California Proposition 65 substances | Not contained |

## Specifications and approvals

|          |                    |
|----------|--------------------|
| UL / CSA | UL 758 AVL2.E42769 |
|----------|--------------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 1  |
| Net weight                     | 4,400 g  |
| Net weight                     | 113 g/m  |
| Country of origin              | USA  |
| European customs tariff number | 85444993                                       |
| GTIN                           | 5713140025462                                  |
| eCl@ss                         | 27061801 Data and communication cable (copper) |
| ETIM                           | EC003249                                       |
| UNSPSC 24.0                    | 26121609                                       |