



tesa[®] ECO FIXATION

Product Information

BNR 56450, 56454, 56451, 56452

Product Description

tesa Double-sided tape ECO FIXATION is a self-adhesive tape for handicraft and carpet laying. It is solvent-free and made from 100% recycled plastic.

Product Features

- Strong double-sided adhesive
- Easy to tear by hand

Environmental aspects:

- 100% recycled plastic
- Solvent-free adhesive
- Packaging made of recycled shrinking foil

Technical Information (average values)

The values in this section should be considered representative or typical only and should not be used for specification purposes.

Product Construction

- | | | | |
|--------------------|------------------|-------------------|--------|
| • Type of adhesive | synthetic rubber | • Total thickness | 160 µm |
|--------------------|------------------|-------------------|--------|

Properties/Performance Values

- | | | | |
|------------------------|---------------|--------------------------|---|
| • Tensile strength | 150 N/cm | • Suitable surfaces | Tiles, Brick, Most plastics, Glass, Acrylic glass, Cardboard, Plaster, Paper, Metal, Steel, Stone |
| • Adhesive strength | High adhesion | | |
| • Residue free removal | no | | |
| • Solvent free | yes | | |
| | | • Temperature resistance | yes |
| | | • Tensibility | 25 % |



tesa[®] ECO FIXATION

Product Information

Disclaimer

tesa[®] products prove their impressive quality day in, day out in demanding conditions and are regularly subjected to strict controls. All information and recommendations are provided to the best of our knowledge on the basis of our practical experience. Nevertheless tesa SE can make no warranties, express or implied, including, but not limited to any implied warranty of merchantability or fitness for a particular purpose. Therefore, the user is responsible for determining whether the tesa[®] product is fit for a particular purpose and suitable for the user's method of application. If you are in any doubt, our technical support staff will be glad to support you.

For latest information on this product please visit <http://l.tesa.com/?cp=NaN>