

NEW!

Available June 2016

HG 2620 E GB 110V (case)

Powerful. Tough. Robust.

- Running time of brushless motor of 10.000 hours!
- Suitable for construction site use
- Display in field of view
- Plug in heating element for a fast exchange
- Ergonomic grip
- Fine dust particle filter included
- Fast and easy exchange of power cord



Image shows HG 2620 E

HG 2620 E GB 110 V (case)

Powerful. Tough. Robust.

Technical Specifications

Power supply:	110 V
Output:	1650 W
Temperature:	50 - 700 ° C, continuously variable in 10 ° C steps
Air pressure:	3.000 Pa
Highlights:	Suitable for construction site use, display in field of vision, plug-in heating element, ergonomic grip, safety heat indicator, fine dust filter enclosed, 4 memory programmes, easy-to-change power cord, LOC function, restart protection
Power cord length:	3 m
Motor:	Brushless motor
Motor life:	10.000 hours
Heating element:	Ceramic heating element
Accessories:	Use of our "Professional accessories"

Weight of packaging:	gross: 2370 g; net: 1160 g
Dimensions of packaging:	395 x 100 x 320 mm
Customs tariff number:	84198998 UL RO
Country of origin:	Romania
Region of origin:	03
Weight of paper packaging:	70 g
Weight of plastic packaging:	1000 g



EAN-Code	Art.-No.	Bezeichnung Description	VE min.order quan.	VE auf Palette pack. Unit/pallet	Palettenhöhe pallet height	Exportpreis/Stk. Export price/pc.
4007841 012601	012601	Hot Air Tool HG 2620 E KF GB 110V	1			