



HANDCRANK HOSEREEL

RA8665

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:08





DESCRIPTION

HANDCRANK HOSEREEL

This hose reel on a 360 ° rotatable metal base has a 30-meter-long air hose (PU) . Maximum pressure of 15 bar. This hose reel has a winch quickly winding the hose. The inside diameter of the PU hose is 8.5mm.

SPECIFIC DATA

Designation	HOSE REEL ON TURNTABLE - 30 METRES
Sales reference	RA8665
Weight (kg)	8.85
Width (mm)	360
Length (mm)	303

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:08



Height (mm)	330
Guarantee	M2 SAM Equipment and Machine Guarantee

Guarantee applied

M2 | SAM Equipment and Machine Guarantee

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

SAM Outillage

10 rue Camille de RochetaillÃ©e
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 â‚¬

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:11:08

