

Features

- LED Panel Light
- Steady White Light
- IP20
- High performance LED
- -20°C to +50°C
- 110-240VAC
- 28 White LED's
- 600 Lumen Light Output
- 4000K Colour Temperature
- Built in Motion Sensor

600 LUMEN MAGNETIC LED PANEL LIGHT 110/240VAC WITH MOTION SENSOR

RS Stock No.: 0736550



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

LED panel light to provide optimal lighting inside electrical control, command, and distribution panels. The LED panel light can be positioned within the control cabinet, directly on a ferromagnetic surface by means of its magnetic base, or on other surfaces by means of a screwed-on magnetic support (supplied with the product).

The LED Panel light can be powered using Voltages: 110-240VAC

Manufactured from Fibreglass reinforced polyamide base and unbreakable polycarbonate dome.

LED panel light is fitted with an optical group of 28 LEDs with an irradiation angle of 120° and 4000K light colour at 600 lumens.

Using the connectors provided, LED panel light can be connected and disconnected simply. This LED Panel light has a built in Motion Sensor which will turn on the LED Panel Light when motion detected. Up to 8 LED panel lamps can be connected in series.

General Specifications

Accessory Type	LED Panel Light
For Use With	Electrical control panels
Material	Polyamide
Special features	600 Lumens Light Output
Mounting type	Surface using bracket or Magnets (included)
Colour	Clear Lens / 4000K White Light

Mechanical Specifications

Dimensions	314 x 60 x 72mm
Weight	35g

Approvals

Compliance/Certifications	CE / UKCA
---------------------------	-----------