



Main

Range	Actassi
Product type	Splitter block

Complementary

Equipment provided	Lockring Plug Pictogram stickers
Location of connection	Technical room
Connector type	1 male RJ45 connector hub 2 female RJ45 connector analog telephone
Width	18 mm
Height	45 mm

Environment

Temperature range	-20...60 °C
-------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations