Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

PUSH BUTTON 600VAC 10A 30MM T-K



9001KR9RH2

Main

Range of product	Harmony 9001K	
Product or component type	Push-button	
Device short name	К	
Operator additional information	Screw-on plastic	

Complementary

Bezel material	Metal	
Mounting diameter	30 mm	
Light source	Without	
Light block supply	Without supply	
Contacts type and composition	2 C/O	
[le] rated operational current	10 A, AC-15 10 A, DC-13	
Contact operation	Standard	
Device presentation	Complete product	
Cap/operator or lens colour	Red	
Operator profile	Mushroom Ø 41 mm	
Type of operator	Push-pull	
Operator position information	2 positions	
Size	30 mm	

Environment

Product certifications	NEMA UL listed file E42259 CCN NKCR CE CSA LR 25490 class 3211 03
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.826 cm
Package 1 Width	5.588 cm
Package 1 Length	9.398 cm

Package 1 Weight 172.365 g

Logistical informations

Country of origin MX

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration

Use Again

○ Repack and remanufacture	
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins