

USB 3.1



Metal flash drive with style and performance.

Store your data with the stylish Lexar® JumpDrive® M45 USB 3.1 Flash Drive. The metal finish serves as both an elegant design and durable protective cover. With fast USB 3.1 transfer speeds up to 250MB/s read¹, you'll quickly transfer files, photos, and videos in no time. Available in capacity options from 32GB to 128GB, this drive also has advanced security software solution to help give you peace of mind knowing your files are safe. It's also backward compatible with USB 3.0 and 2.0 devices, providing added versatility. Five-year limited warranty.



Stylish Metal Design



High Speed Transfer



256-bit AES



Plug-and-Play

Product Highlights:

- Stores and transfers content faster with high-speed USB 3.1 performance
- Stylish metal design with exceptional durability
- Securely protects files using an advanced security software solution with 256-bit AES encryption
- Reliably stores and transfers photos, videos, files, and more
- USB 3.1 (Gen 1) enabled; backwards compatible with USB 3.0 and 2.0 devices
- Compatible with PC and Mac® systems
- Five-year limited warranty

Capacities:

32GB
(up to 250MB/s read)¹

64GB
(up to 250MB/s read)¹

128GB
(up to 250MB/s read)¹



Store and transfer content faster. With fast USB 3.1 performance, this drive delivers speeds up to 250MB/s read¹ so you can get to your content quicker. And for added versatility, the drive is backwards compatible with USB 3.0 and 2.0 devices.

Durable and Stylish. The stylish, elegant metal design also provides you with exceptional durability. The Lexar JumpDrive® M45 is designed for your convenience. It comes with a lanyard or keyring that makes it easy to take it with you on the go.

Security every step of the way. Looking to protect personal information, financial records, or other sensitive files on the go? JumpDrive® M45 includes an advanced security solution with 256-bit AES encryption to help protect your essential files against corruption, loss, and deletion. Easily create a password-protected vault that automatically encrypts data. And for peace of mind, files that are deleted from the vault are securely erased and can't be recovered.

Capacities to store all your data. JumpDrive® M45 comes in a wide range of capacities — 32/64/128GB. These options make it easy to find one to suit your needs and store more of your data in one place.

Rigorously tested. All Lexar product designs undergo extensive testing in the Lexar Quality Labs, facilities with more than 1,100 digital devices, to ensure performance, quality, compatibility, and reliability.

For more than 20 years, Lexar has been trusted as a leading global brand of memory solutions. Our award-winning lineup includes memory cards, USB flash drives, card readers, and solid-state drives. With so many options, it's easy to find the right Lexar solution to fit your needs. Lexar products are available worldwide at major retail and e-tail stores. For more information or support, visit www.lexar.com.

¹ Up to 250MB/s read transfer, write speeds lower. USB 3.1 Gen 1 or USB 3.0 support required. Speeds based on internal testing. Actual performance may vary.

Some of the listed storage capacity is used for formatting and other purposes and is not available for data storage. 1GB equals 1 billion bytes.

Security safeguards, by their nature, are capable of circumvention. Lexar does not guarantee data will be 100% secure from unauthorized access, alteration, or destruction.

www.lexar.com

©2019 All Rights Reserved. Information, products, specifications, and features are subject to change without notice. Neither Lexar nor Longsys is responsible for omissions or errors in typography or photography. Lexar, the Lexar logo, and all other Lexar trademarks are the property of Longsys Electronics (HK) Co., Ltd. or Shenzhen Longsys Electronics Co., Ltd. All other trademarks are property of their respective owners.