



Main

Range of product	OptiLine 45
Cabling installation system	Trunking
Product type	T-piece
Colour	Polar white (RAL 9003)
Quantity package 1 / unit	Set of 1

Complementary

Trunking material	Plastic
Trunking dimension	165 x 55 mm 95 x 55 mm 140 x 55 mm 185 x 55 mm 75 x 55 mm
Fixing mode	Snap-fitted
Product material	PC/ABS
Length	97 mm
Height	52 mm
Width	57 mm

Environment

Standards	73/23/EEC 93/68/EEC EN 50085-1:2005 EN 50085-1:2013/A1 EN 50085-2-1:2006 EN 50085-2-1:2011/A1
Operating temperature	-25...60 °C
IP degree of protection	IP40
IK degree of protection	IK07

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Environmental Disclosure	 Product Environmental Profile
Circularity Profile	No need of specific recycling operations