

Snow Blower XGT®

SN001G

40V, 53 cm

Model SN001G is a snow blower powered by a 40VMax XGT Li-Ion battery.

The walk behind snow blower is 530mm clearing width and 300 mm clearing height. It is compact and lightweight. This reduces burden and time when clearing snow. Features and benefits: Snow throwing distance range of 10m can be adjusted on the deflector angle at the top of the discharge chute. LED lights. Foldable handle for easy storage



Technical specifications

Nominal Battery Voltage	40 V
Voltage XGT	✓
Brushless Motor	✓
No load speed	1400 – 2100 min ⁻¹
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Sound Power Level (L _{WA})	77,52 dB(A)
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Noise Uncertainty (K Factor)	3 dB(A)
Vibration Level (3 axes)	≤ 2,5 m/s ²
Vibration Uncertainty (K Factor)	1,5 m/s ²
Working width	530 mm
Tool weight with battery	17,6 - 18,8 kg
Product net weight	16,9 kg
Product Dimensions (L x W x H):	1370 x 540 x 975 mm

User benefits

- Speed adjustment
- Built-in LED light illuminates the work area
- Ergonomic soft grip handle provides increased comfort
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Cordless foldable handle for quick and compact storage
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing