

General Information

| | |
|------------------------|--|
| Extended Product Type: | 216RPR6 |
| Product ID: | 2CMA168261R1000 |
| EAN: | 7392696682619 |
| Catalog Description: | Socket-outlet with RCD, 6h, 30mA, 16A, IP44, 2P+E |
| Long Description: | Socket-outlet with RCD, earthing sleeve position 6h, 30mA, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Blue |

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Socket Outlets with RCD

Ordering

| | |
|-------------------------|---------------------|
| EAN: | 7392696682619 |
| Minimum Order Quantity: | 1 piece |
| Country of Origin: | Czech Republic (CZ) |

Dimensions

| | |
|---------------------|--------|
| Product Net Width: | 120 mm |
| Product Net Height: | 243 mm |
| Product Net Length: | 149 mm |
| Product Net Depth: | 243 mm |
| Product Net Weight: | 1.2 kg |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 124 mm |
| Package Level 1 Length: | 337 mm |
| Package Level 1 Height: | 153 mm |
| Package Level 1 Gross Weight: | 1.2 kg |
| Package Level 1 EAN: | 7392696682619 |
| Package Level 1 Units: | 1 piece |

Environmental

| | |
|--------------|---|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2007 Q1 |
|--------------|---|

Certificates and Declarations (Document Number)

| | |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information: | 2CMC700001D0002 |
| RoHS Information: | 2CMC700057D0001 |

Additional Information

| | |
|----------------------------------|--|
| Additional Information: | Cable entry, knock-outs 2xØ25mm |
| Cable Cross-Section: | 1.5 ... 4 mm ² |
| Cable Entry Position: | Top |
| Cable Outlets Per Side: | 2xØ25 |
| Color: | Blue |
| Degree of Protection: | acc. to IEC 60529 IP44 |
| Enclosure Material: | Thermoplastic |
| Frequency (f): | 60 Hz |
| Function: | Surface socket outlet with RCD, 30 mA |
| IIT Publishing Status: | Level 0 - Information enabled |
| Invoice Description: | Ind. P&S#216RPR6 |
| Number of Poles: | 3 |
| Number of RCD 30mA: | 1 |
| Number of RCDs: | 1 |
| Object Classification Code: | 2CMT005069 |
| Product Main Type: | RPR |
| Product Name: | Industrial Socket Outlet with Protection |
| Protection Type: | Splashproof |
| Rated Current (I _n): | 16 A |
| Rated Residual Current: | 30mA |

| | |
|---------------------------------------|------------------------------|
| Rated Voltage (U_r): | 200 ... 250 V |
| RoHS Date: | L23 |
| Standards: | IEC 60309-1,-2 |
| Suitable For: | Socket Outlets with RCD |
| Suitable for Product Class: | Industrial Plugs and Sockets |

Classifications

| | |
|------------------|----------|
| E-number: | 2466300 |
| UNSPSC: | 39120000 |

