

NRT4-100K

NeTYS RT 10kVA VFI UPS 1/1 PF=1 WITH BATTERY INTEGRATED +RAILS



Strong points

- Best-in-class design
- Up to 5-year warranty
- Ease of use
- Optimum battery management
- IoT and cybersecurity
- Simple installation within any operating environment
- Li-Ion battery UPS: Compact and resilient
- Li-Ion battery UPS: Faster and longer

General characteristics

- Rack/Tower convertible.
- Embedded dry-contact interface.
- Input/Output cables (1000-3000 VA).
- Rail kit and rack ears.
- USB cable.
- Tower stands.
- Cable lockers.
- Connection for battery extension modules.
- Port for parallel operation (5000 - 10000 VA).
- Internal temperature sensor.
- Power off the UPS remotely.
- Cold start.
- Auto and Manual battery test.

Compliance with standards

- IEC 62040-1
- IEC 62040-2
- IEC 62040-3
- AS 62040.1.1
- AS 62040.1.2
- AS 62040.2
- RCM (E2376)

[Access to resources \(ex: manuals\)](#)

NETYS RT is the fourth generation of single-phase rack-tower UPS, ensuring the protection and availability of IT infrastructure that meets the demands of both power reliability and installation flexibility.

Technical Characteristics

Length of the product unit [mm]	215,3
Width of the product unit [mm]	438
Depth of the product unit [mm]	590
Weight [kg]	75.3
Depth [mm]	590
Height [mm]	215,3
In/out	1/1
Output voltage	230
Rated frequency	50/50
Width [mm]	438
Sn [kVA]	10
Pn [kW]	10
Conf	C1
Input voltage	230
Rate (min)	10
Rate (max)	10
Life Time	03-05
Typical Backup Time [min]	10
Configuration	UPS Single Unit(s) with Bypass

Commerce

Effective date	2025-01-01
Offer Life Cycle Code	40

ETIM - Electrical characteristics

Input voltage [V]	110..276
Primary frequency [Hz]	40..70
Number of phases primary	1
Output voltage [V]	200..240
Secondary frequency [Hz]	50..60
Output effective power [W]	10000
Output apparent power [VA]	10000
Number of phases secondary	1
SNMP	No
Voltage type	AC
Max. voltage distortion output (linear load) [%]	1
Output power factor	1

ETIM - Mechanical characteristics

Height [mm]	215,3
Width [mm]	438
Depth [mm]	590
Weight [kg]	75.3
Construction type	482.6 mm (19 inch) device
Input connection	Fixed connection

Number of output connections fixed connection	1
ETIM - Technical features	
USB interface	Yes
With communication interface RS-232	No
Bridging time full load [min]	4
Suitable for network-management	Yes
USV- technology	Online
Overall efficiency [%]	95.61
Efficiency in eco-mode [%]	98
Potential free switch contact	Yes
Auto shut down function	Yes
Logistics	
GTIN/EAN	8027122831901
Weight of the packing unit [kg]	92.5
Length of the packing unit [m]	0.6
Width of the packing unit [m]	0.7
Depth of the packing unit [m]	0.8
Norms	
Conformity to standards	IEC