

PP-4-38-...

Insulating safety padlock with retaining key, nylon shackle H
38 mm Ø 4 mm

Application :

- For locking the separating devices (e.g. circuit breakers) to prevent their operation.
- Padlock with insulating shackle for use in low voltage 1000 V AC - 1500 V DC: tested and validated in accordance with the electrical test IEC 60900 (2012) §5.5.3. at 5 000 V.
- More secure locking: impossible to drop the key when the shackle is open, the key remains trapped.

Features :

- Available with a keys alike (A1 to A6) or different (Z).
- Marking on both sides:
 1. On one side: Standard symbol.
 2. On the other side: area for marking user names and coordinates.
- Padlock delivered with 2 keys.



Ref.	Description		Diameter	Characteristics
	Color	Key Number	Shackle	Weight
PP-4-38-G-A1	■	A1	4	90g
PP-4-38-G-A2	■	A2	4	90g
PP-4-38-G-A3	■	A3	4	90g
PP-4-38-G-A4	■	A4	4	90g
PP-4-38-G-A5	■	A5	4	90g
PP-4-38-G-A6	■	A6	4	90g
PP-4-38-G-Z	■	Z	4	90g