



# 121073-2307 D

## Part Number Details

ittPartNo	DB-25S-A191-A197
Global Mfg Part No.	121073-2307 D
line	D Sub
series	ORIGINAL D
category	D Sub
brand	Cannon

General	Standard D-Subminiature
Wire Gauge Range AWG	AWG 20-28
Mating Cycles	200
Dielectric Withstanding Voltage	1200 VAC at sea level
Current Rating	7.5 A at 85°C / 5 A at 105°C
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+125°
Salt Spray Test	20 hours
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Contact Arrangement	25 contacts size 20
Gender	Socket
Contact Type	turned
Contact Material	copper alloy

Contact Finish	gold over nickel (Performance Class 2)
Contact Termination	Solder Pot
Mounting Methode	.120" (3,05mm) Through Hole



RoHS compliant

Material restriction according to RoHS Directive 2011/65/EU amended with Directive (EU) 2015/863



REACH SVHC: consult factory

A datasheet is available for download.

[Download Datasheet PDF](#)

Check the stock availability of this product at our distributors.

Check Stock Now

Part Number	Distributor	Qty	Location
121073-2307 D	<a href="#">MUETRON Mueller GmbH &amp; Co. KG</a>	593	Germany

Note: Data provided here are offered in good faith and are as reliable and accurate as possible. However, they do not form part of any contract of supply or purchase unless specifically confirmed in writing by an authorized representative of ITT. All information and images shown are the property of ITT ICS and are not to be reproduced in any form without direct authorization from ITT ICS. ITT ICS strongly recommends that you contact your local ITT Sales Office for confirmation of all the details you obtain through these Web pages. Please be aware that data may change at any time and without notice. For a listing of Sales Offices, local sales support, and authorized distributors please use the "Contact Us" at the top of every page.

ittPartNo: DB-25S-A191-A197; globalManufPartNo: 121073-2307 D; line: D Sub

[Request a Quote](#)