



Main

Range of product	Acti 9
Device short name	iATLc+c
Product or component type	Multilevel centralized control auxiliary
[Uc] control circuit voltage	24...240 V AC 50/60 Hz impulse

Complementary

[Ui] rated insulation voltage	440 V
[Uimp] rated impulse withstand voltage	4 kV
Remote control type	2 entries for switch
Mounting mode	Fixed
Mounting support	DIN rail
9 mm pitches	2
Height	86 mm
Width	18 mm
Depth	71 mm
Colour	White
Connections - terminals	Tunnel type terminals 0.5...4 mm ² - rigid Tunnel type terminals 0.5...4 mm ² - rigid - with cable end Tunnel type terminals 1...4 mm ² - flexible Tunnel type terminals 1...4 mm ² - flexible - with cable end
Wire stripping length	11 mm
Tightening torque	1 N.m
Range compatibility	Acti 9 iTL iTLc Acti 9 iTL iATLc Acti 9 iTL iATLc+s

Environment

Overvoltage category	III
IP degree of protection	IP20 conforming to IEC 60529

Tropicalisation	2
Relative humidity	95 % at 55 °C
Ambient air temperature for operation	-20...50 °C
Ambient air temperature for storage	-40...70 °C
Standards	EN/IEC 60669-2-2

Packing Units

Package 1 Weight	75 g
Package 2 Weight	640 g
Package 3 Weight	6.288 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 months
----------	-----------