

Datasheet

Wall Mounting Kit for Stati-Check RS-212-7618



- Designed to be used with Stati-Check Tester (not supplied)
- Size: 300mm x 435mm
- Thickness: 3mm
- Made of yellow Foamalite
- Backboard printed with RS logo and part number
- Supplied with 4 brass washers and screws
- Stainless steel bracket for Stati-Check Tester affixed to backboard

Physical properties of Foamalite:

Test	Test Method	Units	Average Result
Specific Gravity		g/cm ³	0.55 - 0.70
Determination of Water Absorption	ISO 62: Method 1	%	0.19
Tensile Strength at Yield	ISO R527	MPa	19.37
Elongation at Break	ISO R527	%	17.89
Flexural Modulus	ISO 176	GPa	0.903
Charpy Impact Strength	ISO 179	kJm ⁻²	1.43
Shore D Hardness	ISO 868	Value	63
Heat Distortion Temperature	ISO 75: Method A ISO 75: Method B	°C °C	57.75 68.4
Coefficient of Linear Expansion		°C ⁻¹	0.498 x 10 ⁻⁶
Flame Spread Test	BS 476: Part 7 France: NSP 92501,5 Italy: D Come DA UNI 9176:1998 Germany: DIN 4102	Class	1Y M ₋₁ 1 B ¹

Unless otherwise noted, tolerance ±10%

Specifications and procedures subject to change without notice.