



cupbio maintenance trolley with cupboard / 5 drawers & top tray with mat (400/650). Featuring a heavy duty, reinforced steel housing with double, independent, storage sections, push - pull handle, 100% extension drawers with drawer blocking and 125mm diameter castors. Drawer configuration: 2x 75mm, 1x 100mm, 1x 150mm, 1x 200mm (50kg U.D.L.) and cupboard section with 1 doors and 1 galvanised steel shelf (100kg U.D.L.). Finished in durable powder coat paint in RAL 7035 light grey / RAL 3004 crimson red. WxDxH: 1050x525x885mm

Breite [mm]: 1050
Tiefe [mm]: 525
Höhe [mm]: 885
Bruttogewicht [kg]: 101.86
EAN-Code: 5039350057902
Zolltarifnummer UK: 94032080
Ursprungsland: GB

Produkteigenschaften

Product surface	Powder coated
Product material	Sheet steel
Main colour	Crimson red
Main RAL colour	RAL 3004
Secondary colour	Light grey
Secondary RAL colour	RAL 7035

Artikelbeschreibungen

Product brand	cupbio
---------------	--------

Schubladen

Number of drawers	5
Drawer load capacity [kg]	50
Drawer height 1 [mm]	75
Drawer height 2 [mm]	75

Drawer height 3 [mm]	100
Drawer height 4 [mm]	150
Drawer height 5 [mm]	200

Schrank, Gehäuse, Werkbank und EAP

Worktop/housing top type	Top tray and mat
Shelf load capacity [kg]	100
Door type	Perfo
Door height 1 [mm]	700