





5	BODY	1	BRASS	NICKEL				
4	INSULATOR	1	TEFLON	NONE	UNLESS OTHERWISE SPECIFIED  1.REMOVE ALL BURRS.	* MAJOR DIMENSION UNLESS OTHERWISE	APPROVED	
3	PIN	1	BRASS	GOLD	12 BREAK ALL CONNERS &	NOTED TOLERANCES 0.5-6=±0.2	CHECKED	
2	GASKET	1	SILICONE	RED	THREADS 45'.	6-30=±0.4 30-120=±0.6	22.110	TITLE SMA MALE TO IPEX MHF1 MALE
1	SHELL	1	BRASS	NICKEL	CENTERS. TO BE CONCENTRIC WITHIN 0.1 T.R. J.ALL DIMENSIONS ARE	120-315=±1.0 ANGLES=±1°	andrew	DRAWING NO. ADAPT/SMAM/IPEX REV A
NO	Description	Q'ty	Material	Finish	5.ÄLL DIMENSIÖNS ARE AFTER PLATING.	SCALE 5/1 UNIT MM	DRAWN DATE	FILE NO.