



Plummer block housing units RSHE35-XL-N (Series RSHE)

cast iron housing, radial insert ball bearing with eccentric locking collar, R seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (https://www.schaeffler.de/content.schaeffler.de/en/news_media/index.jsp) or by telephone on +49 (91 32) 82 - 28 97.

d	35 mm
L	103 mm
H ₂	93 mm
A	45 mm
A ₁	27 mm
B ₁	51,3 mm
d _{3 max}	55 mm
H	47,6 mm
J	82,6 mm
K	M10
Q	Rp1/8

S ₁	32,5 mm	
m	1,38 kg	Mass
C _r	27500 N	Basic dynamic load rating, radial
C _{0r}	15300 N	Basic static load rating, radial
	SHE07	Designation of housing
	GE35-XL-KRR-B	Designation of bearing
	KASK07	Bearing end cap, closed design. To be ordered separately.
		Slot for bearing end cap



