

Features

-
-
-
-
-

RS PRO Cable Trunking

RS Stock No.: 301-1924, 301-1930, 301-1946, 301-1968, 301-1974, 301-1980, 301-1996, 301-2006, 301-2034, 301-2040, 879-3713, 879-3722, 758-9260



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Test to UL file E97527 up to 50 °C.*
- *Supplied complete with cover.*
- *These devices are for routing of wires within devices in factory installations.*
- *Features parallel holes on both sidewalls to facilitate cutting in wire application.*
- *Easy to insert, adding or removing wires - even with terminations attached.*
- *Save your total cost for during installation, wire tracing and circuit troubleshooting.*

General Specifications

Material	High impact, warp-proof PVC , self-extinguishing
Color	Grey
Maximum service temperature	85°C

Approvals

Declarations	UL approved 94V-0.
--------------	--------------------

Similar Products

RS Article No	W(mm)	H(mm)	A	Slot	Length
3011924	25	25	10	8mm	2M
3011946	33	45	14		
3011930	25	45	10		
3011974	50	50	22.5		
3011968	45	45	20		
3011980	25	65	10		
3012006	60	60	27.5		
3011996	45	65	20		
3012040	33	100	14		
3012034	72	64	33.5		
8793713	25	25	10	8mm	1M

8793722	60	60	27.5		
7589260	15	25	5	8mm	2M

Bottom Size

