

232RAU12W

Panel mounted socket

2CMA166952R1000



Socket-outlet, panel mounting, earthing sleeve position
1earthing sleeve position 2h, rated current 32A, IP67
watertight, unified flange, angled, 2-poles+earth, frequency
50-60 Hz, color code Grey

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA166952R1000
Function	Socket outlet, panel mounting, unified flange, angled
EAN	7392696669528
Catalog Description	Socket-outlet, panel mounting, 12h, 32A, IP67, unified flange, angled, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416720
E-Number Norway	2416720
E-Number Sweden	E2416720
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	95 millimetre
Product Net Height	117 millimetre
Product Net Length	117 millimetre
Product Net Depth	117 millimetre
Product Net Weight	0.276 kilogram

TECHNICAL

Product Main Type	TRAU
Color	Grey
Number of Poles	3
Clock Position	12Hour
Rated Current	32 ampere
Rated Voltage	Isol. Transformer volt
Frequency	60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...10 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.323 kilogram
Package Length	112 millimetre
Package Units	box 1 piece