

XEVOX PROFI VDS Motion Detector

BW8010



Specifications

Installation	Wall	Detection method	PIR
Detection range (m)	15 x 15	Alarm memory	Yes
Immune to animals	No	Power consumption	11 mA
Voltage supply	12 V	Alarm contact	NC, 50 mA, 24 V DC
Tamper contact	NC, 100 mA, 24 V DC	Temperature range	-10° to 55 °C
VDS	G106505	VSÖ	GS-N060614/01E