

## Datasheet

# RS Pro Stainless Steel Bolt Anchor M16, fixing hole diameter 16mm, length 130mm

RS Stock No: **622-2010**



## Product Details

RS Pro captive stud bolt anchor made of A4-316 grade stainless steel resist corrosion. This bolt anchor is suitable for use in concrete with a compressive strength greater than 20 N/mm<sup>2</sup>. The bolt anchor measures 130 mm long with M16 threading that is suitable for 16 mm fixing hole diameter.

## Features and Benefits

- Captive stud through bolt anchor
- A4-316 grade stainless steel construction
- Suitable for use in concrete over 20N/mm<sup>2</sup>
- Fixing hole diameter of 16 mm
- 130 mm length



**Specifications:**

Material	Stainless Steel
Type	Captive Stud Through Bolt Anchor
Fixing Hole Diameter	16 mm
Length	130 mm
Maximum Fixing Thickness	10 mm
Thread Size	M16
Grade	316 (A4)
Minimum Hole Depth	110 mm