

Anti-vandal pushbutton Ø19 mm

DOMED	Screw terminal			DOMED	Pin terminal		
	FLUSH				FLUSH		
	RAISED				RAISED		

Replace the symbol by the code of the desired material

S	Stainless steel
N	Nickel plated brass
G	Gold plated brass
SB	Brushed stainless steel
A	Al alloy black (colored button)



The Front Shape	Domed / Flush / Raised Round
Contact function:	Momentary
Terminal Type	Screw terminal or Pin Terminal(2x0.5mm)
Switching rate max:	2A / 36VDC
Contact Configuration:	1NO (1NC made to order)
Contact Resistance	≤50mΩ
Insulation Resistance	≥1000MΩ
Dielectric Strength	2000VAC
Operating Temp	-20°C / +55°C
Mechanical lifetime	1,000,000 cycles
Electrical life	200,000 cycles
Panel Thickness	1~10mm
Torque	5~14Nm
Actuating force	About 4N
Operation travel	About 1.8mm
IK Degree / IP Degree	IK09/IP65

Material	Contact	Silver Alloy
	Button	Replace the symbol by the code of the desired material
	Body	
	Base	PBT
LED Spec:	Type	Non-Illuminated
	Rated Voltage	
	Color	
	Life	

Contact arrangement: **1NO**

Switching Operation

LED PIN

Double-break slow-motion contact

NO = normal opened
NC = normal closed