

3550-55 UK

Torque wrench TORCOFLEX UK

1-550 Nm

Code	ETIM
2958082	EC002132
EAN	UNSPSC
4002805935590	27-11-17-15
Country of origin	eCl@ss
Germany	21-04-02-22
Customs tariff number	
82041100	



Article description

- Adjustable, releasing and sturdy tubular torque wrench with integrated lever ratchet (from 3/4 inch with change disk) and with square drive for industry and the trades
- Classified to DIN EN 6789: 2017 type II class A calibrated to a max. admissible deviation of +/- 3 % and therefore more precise than +/- 4 % required by the standard
- Incl. test certificate according to DIN EN ISO 6789-2:2017
- For controlled clockwise tightening

Article information

Contents (Qty of pieces)	1	Torque range (min./max.) [N·m]	110 Nm - 550 Nm
Net weight [kg]	3,7 kg	Trigger mechanism	Short path triggering
Total length [mm]	1.000 mm	Precision +/-	+/- 3 %
Total width [mm]	69 mm	Direction of tightening	Right
Total height [mm]	65 mm	Fixed setting	no
Material	Steel tube construction with high-quality plastic parts	Test certificate	DIN EN ISO 6789-2:2017
Drive connector square (male)	3/4"	Graduation	10
Drive connector square (male)	20 mm	Head height 1 [mm]	36 mm
Return angle	7,2 °	Width of head 1 [mm]	68,0 mm
Number of teeth	50	Calibration length	894,7 mm
Drive type/drive	Reversible ratchet	vernier Nm	1 Nm
Torque (min.) [N·m]	110 Nm	Distance housing - square drive	34 mm
Torque (max.) [N·m]	550 Nm		