

**FAG****6208-2Z-L069-C3**

Deep groove ball bearing

Deep groove ball bearing 62...-2Z, single row, shields, steel sheet metal cage

Technical information



Your current product variant

Sealing	2Z	Non-contact shield on both sides
Cage	JN	Steel sheet metal
Tolerance class	PN	Normal (PN)
Dimensional / heat stabilization	SN	Rings dimensional stabilized up to 120°
Lubricant	L069	Low noise high-temperature grease, interchangeable with grease L207
Radial internal clearance	C3 (Group 3)	Internal clearance larger than CN
Bore type	Z	Cylindrical

Main Dimensions & Performance Data

d	40 mm	Bore diameter
D	80 mm	Outside diameter
B	18 mm	Width
C _r	31,000 N	Basic dynamic load rating, radial
C _{0r}	17,800 N	Basic static load rating, radial
C _{ur}	1,080 N	Fatigue load limit, radial
n _G	10,400 1/min	Limiting speed
n _{gr}	9,300 1/min	Reference speed
m	372 g	Weight



Mounting dimensions

d a min	47 mm	Minimum diameter shaft shoulder
D a max	73 mm	Maximum diameter of housing shoulder
r a max	1 mm	Maximum fillet radius

Dimensions

r min	1.1 mm	Minimum chamfer dimension
D 1	67.6 mm	Shoulder diameter outer ring
D 2	70.36 mm	Caliber diameter outer ring
d 1	52.95 mm	Shoulder diameter inner ring

Temperature range

T min	-30 °C	Operating temperature min.
T max	120 °C	Operating temperature max.

Calculation factors

f 0	14	Calculation factor
-----	----	--------------------

Characteristics

	Radial load
	Axial load in one direction
	Axial load in two directions
	Lifetime lubrication, freedom from maintenance
	Grease Lubrication
	Sealed on both sides