








THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

- .04FEB03

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION		DATE	DWN	APVD
FB	00	O	RELEASED	FB00-0015-03	04FEB03	JJ TS



TOLERANCES UNLESS OTHERWISE SPECIFIED:

10 > * : ±0.2
 30 > * > 10 : ±0.25
 100 > * > 30 : ±0.3
 ANGLE : ±3°

NOTES:

1. MATERIAL:

HOUSING: NYLON(G.F.) UL94V-0, COLOR: GRAY,BLUE
 POST: PRE-TIN 0.5mm SQ. BRASS WIRE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
MM	
0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
MATERIAL	FINISH
SEE NOTE 1	SEE NOTE 1

DWN	S. YAO	31JAN03
CHK	S. YAO	31JAN03
APVD	T. SASAKI	31JAN03
PRODUCT SPEC	108 - 60018	
APPLICATION SPEC	114 - 5223	
WEIGHT	SEE TABLE	
CUSTOMER DRAWING		

Tyco Electronics Corporation		SHANGHAI, CHINA	
NAME		AMP Mini CT Connector 1.5mm Pitch	
SIZE		Double Row Post HDR Ass'y (V)	
CAGE CODE		DIP Staggered Type with Boss with Kink	
DRAWING NO		RESTRICTED TO	
A3 00779		C-292208	
SCALE		SHEET 1 OF 2	
REV		0	

LOC	DIST	REVISIONS					
FB	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

1.67	35.5	34.1	28.5	40	9-292208-0	4-292208-0
1.60	34.0	32.6	27.0	38	8-292208-8	3-292208-8
1.53	32.5	31.1	25.5	36	8-292208-6	3-292208-6
1.46	31.0	29.6	24.0	34	8-292208-4	3-292208-4
1.38	29.5	28.1	22.5	32	8-292208-2	3-292208-2
1.31	28.0	26.6	21.0	30	8-292208-0	3-292208-0
1.24	26.5	25.1	19.5	28	7-292208-8	2-292208-8
1.17	25.0	23.6	18.0	26	7-292208-6	2-292208-6
1.10	23.5	22.1	16.5	24	7-292208-4	2-292208-4
1.03	22.0	20.6	15.0	22	7-292208-2	2-292208-2
WEIGHT (g)	C	B	A	Pos.	BLUE	GRAY
	DIMENSIONS				PART NO	

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

BY TYCO ELECTRONICS CORPORATION.

COPYRIGHT -



THIS DRAWING IS UNPUBLISHED.

©

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

-

DIMENSIONS: MM		DWN —	MATERIAL —		FINISH —	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK —	Tyco Electronics Corporation SHANGHAI, CHINA			
0 PLC ± — 1 PLC ± SEE SHEET 2 PLC ± 1 OF 2 3 PLC ± — 4 PLC ± — ANGLES ± —		APVD —	NAME AMP Mini CT Connector 1.5mm Pitch Double Row Post HDR Ass'y (V) DIP Staggered Type with Boss with Kink			
		PRODUCT SPEC —	SIZE A4			
		APPLICATION SPEC —	CAGE CODE 00779			
		WEIGHT —	DRAWING NO C-292208			
		RESTRICTED TO —				
CUSTOMER DRAWING			SCALE NON		SHEET 2 OF 2	
					REV 0	

AMP 1489-35 REV 31MAR2000