



### Main

Range of product	Multifix
Product name	Multifix Air
Product or component type	Apparatus box
Device application	For airtight installation
Device presentation	Without cover
Quantity per set	Set of 40

### Complementary

Function available	Anti-rotation system
Number of gangs	1 gang
Fixing mode	By screws
Material	PP/TPE
Mechanical robustness	Airtight Fire resistance
Colour tint	White (RAL 9010)
Cable entry	2 knock-outs conduit of 16...20 mm diameter 2 knock-outs conduit of 20...25 mm diameter
Distance between centers	71 Mm
Diameter	67 Mm 47 mm
Distance between supports	60 Mm
Height	71 Mm
Width	71 Mm
Depth	47 Mm

### Environment

Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP40
Environmental characteristic	Halogen free
Fire resistance	850 °C
Standards	EN 60670-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	26 G
Package 1 Height	4.5 Cm
Package 1 width	7 Cm
Package 1 Length	7 Cm
Unit Type of Package 2	BB1
Number of Units in Package 2	40
Package 2 Weight	1.23 Kg
Package 2 Height	21 Cm
Package 2 width	25 Cm
Package 2 Length	29 Cm
Unit Type of Package 3	P12
Number of Units in Package 3	1920
Package 3 Weight	70.8 Kg
Package 3 Height	80 Cm
Package 3 width	80 Cm
Package 3 Length	120 Cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

Product Life Status : **Commercialised**