

1696A

spirit levels made from die-cast aluminium, with 1 ground base and 2 unbreakable vials, accuracy: 1 mm/m

- Precision 1 mm/m
- Adjustable horizontal vial

|  | art. | L mm | H mm | S mm | g |
|---|------------|---------|---------|---------|-----|
| 016960103 | 1696A 300 | 300 | 43 | 23 | 285 |
| 016960104 | 1696A 400 | 400 | 43 | 23 | 340 |
| 016960105 | 1696A 500 | 500 | 43 | 23 | 430 |
| 016960106 | 1696A 600 | 600 | 43 | 23 | 500 |
| 016960110 | 1696A 1000 | 1000 | 43 | 23 | 800 |

