



Datasheet

Stock No: 415-5996

RS Pro Round Tube 15° to 60° Connector, strut profile Type 3



Product Details

Variable Elbow 15° to 60°

Allows a staircase rail tube to be fixed at any angle between 15° and 60° from the horizontal Alternative to bending the tube

Dimensions (mm)					
Tube Size Ref.	В	С	D	Е	
1	65	60	13	50	
2	80	66	16	55	
3	90	79	17	68	

Note

The 'selection guide' table links the alphabetical key in the illustration to the specific fittings (a typical stock number is also quoted).





Specifications

Structural Element Type	Round Tube
Connector Type	15° to 60° Connector
Fits Strut Profile	Type 3
Fits Tube Diameter	48.3mm
Product Family	RS Handrail System
Material	Cast Iron
Product System	124

Selection Guide			
Key	Fitting Description	Typical Stock No.	
Н	90° Elbow	286-3370	
M	Rail Base Flange	286-3623	
Q	Single Mesh Panel Clip	415-7037	
S	Handrail bracket	286-3689	
Т	Single swivel combination	286-3522	
U	Double swivel combination	286-3544	
٧	√ariable elbow 15° to 60°	415-5968	
W	Adj. Short tee 30° to 60°	415-6006	
Х	Two socket cross adj. 30° to 45°	415-6034	
Υ	Short tee swivel	415-6191	
Z	Plastic stop end	286-3718	