

HD 428

Blocks outside noise

Closed-back around-ear stereo headphones with dynamic bass and high passive noise attenuation



Want a pair of headphones that sound as good as they look? Look no further for the HD 428 comes with a crosshair design and rugged rubber finishing on their earcups, but their high-output neodymium magnets provide for a powerful stereo sound reproduction. Not to forget, their closed circumaural configuration effectively blocks outside noise while the single-sided cable reduces tangling, ensuring high comfort and ease-of-use.

- ▶ **High-output neodymium magnets**
For stereo sound with powerful bass
- ▶ **Closed circumaural headphone design**
Blocks outside noise
- ▶ **Crosshair rubber finishing on earcups**
For long lasting strength and durability
- ▶ **Single sided cable**
For convenient handling

Technical Data



Model	HD 428
EAN	40 44155 04347 1
UPC No.	6 15104 16793 3
Article Number	502765
Transducer principle	Dynamic, closed
Frequency response	18-22000 Hz
Impedance	32 Ω
THD	<0.1% (1kHz/100dB)
Sound pressure level (1 kHz / 1V _{rms})	110 dB (1kHz/1V _{rms})
Weight	390 gm
Cable length	3 m single-sided OFC cable with 3.5 mm gold straight plug / 6.3 mm gold adaptor plug
Connector	3.5 mm straight plug
Content of Delivery	HD 428 headphones 6.3mm adaptor plug
Packaging	
Design	Blister
Dimensions of individual pack (W x H x D)	205 x 235 x 95 mm
Dimensions of multi-pack (W x H x D)	642 x 460 x 286 mm
No. of products per multi-pack	12
Packaging languages	English, German, French, Spanish, Italian, Dutch & Portuguese

iPhone and iPod are trademarks of Apple Inc., registered in the U.S. and other countries.