

# GDS 18 V-200 C Professional



Specification	
Torque, max.	200 Nm
No-load speed (1st gear / 2nd gear)	0 – 1100 / 2300 / 3400 rpm
Rotation:	Forward / Reverse
Max Impacts Per Min	0 – 4000
Battery voltage	18 V
Bit holder/ shank	1/2" Squaredrive with pinhole and friction ring
Head Length	134 mm
LED light	Yes
Part number	06019G4370

Key Product Features	Consumer Benefit
Powerful and compact	Powerful use even in hard to reach areas thanks to best head length to torque ratio
Intelligent	Bluetooth connectivity module for tool feedback, Soft Start and service information via mobile
Brushless Motor	longer run time and lifetime thanks to the brushless EC motor with electronic motor protection
Enduring	Longer runtime & lifetime thanks to brushless EC motor with Electronic Motor Protection (EMP)
Flexible power system	All batteries of the same voltage work with all tools in the range
3 year tool warranty and 2 year battery warranty*	100% consumer confidence



**You Tube** [youtube.com/BoschProfessionalUK](https://www.youtube.com/BoschProfessionalUK)

**f** [facebook.com/BoschProfessionalPowerToolsUK](https://www.facebook.com/BoschProfessionalPowerToolsUK)



**BOSCH**

Invented for life

\* Please register your tool, lithium-ion battery or charger online within four weeks of purchase to become eligible for the warranty services Bosch provide