

7220 // ULTIMATE STEP MID FIT

Boots
PPE risk category II



Waterproof and breathable SECONAMICS membrane
Well padded bootleg for optimal fit and comfort
TPU reinforcement at heel



S7S

CI

FO

SC

SR



SECONAMICS



7220 // ULTIMATE STEP MID FIT



Shoe upper:	Action Leather, black TPU, black
Outsole:	PU / TPU, black / transparent
Size(s):	36-48
Packaging unit:	5 pair(s)
Certification:	EN ISO 20345, EN IEC 61340-4-3

NITRAS ULTIMATE STEP MID FIT, safety boots, half-height, S7S CI FO SC, durable Action Leather, black, durable PU / TPU outsole, black / transparent (colour code: 1000), fibreglass toe cap, textile perforation resistant midsole, metal-free, premium COMFORT STEP insoles, ergonomically formed, with dial fastener 711 // FIT SYSTEM for fast availability and optimal fit, waterproof and breathable SECONAMICS membrane, highest slip resistance (SR), width 11, well padded bootleg for optimal fit and comfort, reflective elements, heel lining for easy donning and doffing and heel reinforcement made of robust microfibre, additional toe cap, TPU reinforcement at heel, premium quality, DGUV Rule 112-191-proofed, Type 1, ESD-capable, PPE risk category II

EN ISO 20345

EN IEC 61340-4-3



S7S

CI

FO

SC

SR



SECONAMICS



Industries

-  Craft
-  Building / Construction
-  Landscape gardening
-  Transport / Logistics
-  Waste management
-  Refrigeration range

Advantages

- + Waterproof and breathable SECONAMICS membrane
- + Well padded bootleg for optimal fit and comfort
- + TPU reinforcement at heel



Further images



Additional information

Miscellaneous

Weight 743

Logistics data

Size	GTIN (SPU)	GTIN (PU)	Length (m)	Width (m)	Height (m)	Weight (kg)	Quantity PU / pallet
36	4059904207752	4059904207882	0,62 m	0,43 m	0,34 m	7,25 kg	16
37	4059904207769	4059904207899	0,62 m	0,43 m	0,34 m	7,55 kg	16
38	4059904207776	4059904207905	0,62 m	0,43 m	0,34 m	7,85 kg	16
39	4059904207783	4059904207912	0,62 m	0,43 m	0,34 m	8,15 kg	16
40	4059904207790	4059904207929	0,62 m	0,43 m	0,34 m	8,45 kg	16
41	4059904207806	4059904207936	0,62 m	0,43 m	0,34 m	8,75 kg	16
42	4059904207813	4059904207943	0,62 m	0,43 m	0,34 m	9,05 kg	16
43	4059904207820	4059904207950	0,645 m	0,45 m	0,375 m	9,35 kg	16
44	4059904207837	4059904207967	0,645 m	0,45 m	0,375 m	9,65 kg	16
45	4059904207844	4059904207974	0,645 m	0,45 m	0,375 m	9,95 kg	16
46	4059904207851	4059904207981	0,645 m	0,45 m	0,375 m	10,25 kg	16
47	4059904207868	4059904207998	0,645 m	0,45 m	0,375 m	10,55 kg	16
48	4059904207875	4059904208001	0,645 m	0,45 m	0,375 m	10,85 kg	16

Customs tariff number: 64039113900

Country of origin: China