



Switches > Rocker Switches



Switch Type: **High Power Rocker Switch**
Product Mount Type: **Panel Mount**
Indicator/Imprint Legend: **None**
Panel Cutout Size: **13.8 x 27.6 mm [.545 x 1.086 in]**
Switch Contact Plating Material: **Silver**

Features

Product Type Features

Switch Type	High Power Rocker Switch
Actuator Type	Top
Actuator Style	Rocker
Switch Connection Type	Quick Connect Terminal

Configuration Features

Indicator/Imprint Legend	None
Panel Cutout Size	13.8 x 27.6 mm[.545 x 1.086 in]
Configuration (Pole-Throw)	Single Pole - Single Throw
Operating Function	On Off

Electrical Characteristics

Contact Current Rating	16 A
Operating Voltage Range	125 VAC

Body Features

Product Orientation	Vertical
---------------------	----------



Actuator Color	Black
----------------	-------

Contact Features

Terminal Tab Width	6.35 mm[.24 in]
Switch Contact Plating Material	Silver

Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	No
----------------	----

Industry Standards

Compatible With Agency/Standards Products	VDE
Compatible With Approved Standards Products	UL E46765

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1571091-4
PRBSA1-16L-BB000=POWER ROCKER



TE Part # 1571092-3
PRBSB1-16F-BA000=POWER ROCKER



TE Part # 1571091-2
PRBSA1-16F-BB0BW=POWER ROCKER



TE Part # 1571091-3
PRBSA1-16F-BB0CW=POWER ROCKER



TE Part # 1571091-9
PRBSA1-16F-BB0HW=POWER ROCKER



TE Part # 1571094-7
PRBSD3-16F-BW000,POWER ROCKER



TE Part # 1571094-4
PRBSD3-16F-BB000,POWER ROCKER



TE Part # 1571092-1
PRBSB1-16F-BR000=POWER ROCKER

Customers Also Bought



TE Part #1-87631-4
18 MODIV HSG DR MKRD .100 POL



TE Part #1123343-2
025 REC CONTACT GOLD FORMING



TE Part #2-2834461-8
MINI DYNAMIC REC HSG ASSY 28P X-KEY BLK



TE Part #6-103635-0
11 MTE HDR SRRA LTCH.100CL LF



TE Part #1-1415899-3
RZ03-1A4-D005



TE Part #2304372-2
1-PORT MATENET HDR ASSY 90DEG, COD B



TE Part #3-640601-2
02P MTA156 CONN ASSY 22AWG LF



TE Part #2098762-4
Contact,female0.64, 22 AWG, CuNiSi, Sn



TE Part #3-2176452-9
CPF 0201 1K33 0.1% 25ppm 1K RL



TE Part #1833011-1
RZF1-1A4-L005

Documents



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1571091-1_G.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1571091-1_G.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1571091-1_G.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English