



# Product data sheet

Power tools for trade & industry

HGS 85/100

## INDUSTRIAL HGS 85/100



### The most important data

|                                 |           |
|---------------------------------|-----------|
| Permitted sanding disc diameter | 125 mm    |
| No-load speed                   | 6,800 rpm |
| Rated power, output             | 1,500 W   |

**Part Number** 0 602 242 234

## Technical data

### Technical data

|                                 |               |
|---------------------------------|---------------|
| Frequency                       | 300 Hz        |
| Voltage                         | 200 V         |
| Permitted sanding disc diameter | 125 mm        |
| No-load speed                   | 6,800 rpm     |
| Rated power, input              | 1,800 W       |
| Rated power, output             | 1,500 W       |
| Rated current                   | 6.4 A         |
| Weight as per EPTA              | 6.3 kg        |
| Toolholder, drive end           | M14           |
| Switch version                  | Safety switch |

# Product data sheet

## Power tools for trade & industry

---



**BOSCH**  
Invented for life

---

You can find more information about the deviations in the following link: <https://www.bosch-professional.com/gb/en/wac/>

