

## Datasheet

### **RS Pro 1 Phase 170VA Variac, 1 Output, 240V**

RS Stock No: **890-2765**



## Product Details

RS Pro 1-phase 170 VA variac is a professional range of open style variable transformer available in either single or three phase. This transformer is not designed to provide mains isolation but does not operate at mains voltage. It has a primary voltage of 240 V and single output. The transformers need to be fitted within an enclosure or a protected environment. This variac meets RoHS compliant.

## Features and Benefits

- Single or three phase versions available in a range of current ratings
- Heavy duty construction
- High efficiency & excellent regulation
- No waveform distortion
- Silver plated commutator
- Overload capacity
- Negligible maintenance
- Trouble free long life

**Specifications:**

Construction	Open
Diameter	83 mm
Dimensions	83 x 80 mm
Knob Rotation	Clockwise
Length	80 mm
Maximum Operating Frequency	60 Hz
Minimum Operating Frequency	50 Hz
Mounting Type	Surface
Number of Outputs	1
Number of Phases	1
Power Rating	170 VA
Primary Current Rating	0.7 A
Primary Voltage Rating	240 V ac
Protection Features	-
Secondary Voltage Rating	0 to 240 V ac, 0 to 270 V ac
Standards Met	RoHS Compliant
Termination Type	Termination Wire
Weight	1.4 kg